

# KERN HB0100-0.

Handlicher Shore-Durometer mit Schleppzeiger

**KERN**<sup>®</sup>



## Measuring system

Measuring range (Max):	100
Precision (of [Max]):	3 %
Readout:	1
Weighing units:	Shore 0

## Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C

## Category

Brand:	Sauter
Category:	Hardness testers

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	180 x 120 x 50 mm
Gross weight:	480 g
Net weight:	160 g
Shipping method:	Parcel service

## Construction

Casing material:	metal
Overall dimensions mounted (WxDxH):	115 x 60 x 25 mm