

# KERN FCF3K-4

Kompakte Tischwaage mit vielseitigen Funktionen und hoher Genauigkeit für Industrie & Gastronomie



## Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readout [d]:	100 mg
Recommended adjusting weight:	2 kg (M1); 1 kg (M1)
Reproducibility:	100 mg
Resolution:	30000
Stabilisation time:	3 s
Tare range:	3 kg
Warm up time:	2 h
Weighing range [Max]:	3 kg
Weighing system:	Strain gauge
Weighing units:	dwt g lb mo oz ozt tl (HK) tl (Tw) tol

## Display

Display digit height:	2,500 cm
-----------------------	----------

## Counting

Counting resolution:	15000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

## Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Charging time:	16 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	20 h
Operating time (Backlight off):	120 h
Operating time (Backlight on):	80 h
Rechargeable battery:	Rchrg. battery optional

## Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

## Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	335 x 400 x 185 mm
Gross weight:	3,350 kg
Net weight:	2,670 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	270 x 345 x 106 mm
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	270 x 345 x 106 mm
Weighing surface (WxD):	253 x 228 mm