

KERN HTS3T-3AM

Robuste Industrie-Kranwaage bis 10 Tonnen mit Eichzulassung [M]



Technical data about verification

| | |
|---|---------|
| Minimum load [Min]: | 20 kg |
| Periodic Verification for Italy: | 969-112 |
| Verification approval conforming to 2014/31/EU: | yes |
| Verification by KERN possible: | yes |
| Verification class: | III |
| Verification value [e]: | 1 kg |

Functions

| | |
|-------------------|-----|
| Standby function: | yes |
|-------------------|-----|

Environmental conditions

| | |
|--------------------------------|--------|
| Maximum humidity: | 95 % |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | -20 °C |
| Minimum humidity: | 10 % |

Power supply

| | |
|----------------|-------------------|
| Charging time: | 12 h |
| Input voltage: | 110 V - 230 V AC |
| n/a: | AUS CH EURO UK US |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Power supply

| | |
|---------------------------------|-------|
| Operating time (Backlight off): | 150 h |
| Operating time (Backlight on): | 100 h |

Service

Adjustment at the location of installation: 961-252

| | |
|--------------------|----------|
| DAkkS Certificate: | 963-132H |
| Verification: | 950-132H |

Category

| | |
|----------------|-------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Crane scale |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 300 x 550 x 250 mm |
| Gross weight: | 10 kg |
| Net weight: | 8,500 kg |
| Shipping method: | Parcel service |
| UN number: | 2800 |

Measuring system

| | |
|-----------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 1 kg |
| Precision (of [Max]): | 0,001 |
| Readout [d]: | 1 kg |
| Reproducibility: | 1 kg |
| Resolution: | 3000 |
| Stabilisation time: | 2 s |
| Warm up time: | 10 min |
| Weighing range [Max]: | 3 t |
| Weighing system: | Strain gauge |
| Weighing units: | kg |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,500 cm |
|-----------------------|----------|

KERN HTS3T-3AM



Robuste Industrie-Kranwaage bis 10 Tonnen mit Eichzulassung [M]

Construction

| | |
|--|-----------------------|
| Casing material: | Cast aluminium alloys |
| Dimensions of display device (WxDxH): | 270 x 175 x 190 mm |
| Overall dimensions mounted (WxDxH): | 200 x 181 x 407 mm |