

## Datasheet

Item no. 1806650 1806646 1806647 1806649 1806648  
1806651 1806645

V1\_10082018\_01\_en

### Buzzer, dia 22mm

	Item No.	Light Colour	Operating Voltage
Buzzer	1806650	Red	24V dc
	1806646	White	24V dc
	1806647	Red	230V ac
Buzzer with Flash	1806649	Red	12V dc
	1806648	Red	24V dc
	1806651	Red	230V ac
	1806645	White	230V ac

Sound intensity:	≥80dB(10cm)
Frequency	2300±300 Hz
Electrical Life	≥30000 hours
Permitted Voltage	±20%(≥110V)
Dielectric Strength:	2.5kV(AC RMS), 1min
Usage Frequency(AC):	50~60Hz
Rated Operating Current:	≤20mA
Brightness:	≥100cd/m <sup>2</sup>
Comparative Tracking Index:	CT1≥100, flame retardant
Insulation Resistance:	U <sub>i</sub> ≤60V, 5MΩ: 60V < U <sub>i</sub> ≤660V, 50MΩ
Light Color:	Red, White
Operating Temperature:	-25°C to 55°C