








Rating	10A 125V, 6A 250V AC	Mount Hole	Circuit Structure												
Contact R	50m ohm Max.														
Insulation R	DC 500V 100M ohm Min.														
Electric Strength	AC 1500V 1 minute														
Circuit	2P SPST OFF-(ON)	<table border="1"> <tr> <td>Thickness</td> <td>X</td> <td>Y</td> </tr> <tr> <td>0.75...1.25</td> <td>19.2-0.1</td> <td>13+0.1</td> </tr> <tr> <td>1.25...2</td> <td>19.4-0.1</td> <td>13+0.1</td> </tr> <tr> <td>2...3</td> <td>19.8-0.1</td> <td>13+0.1</td> </tr> </table>	Thickness	X	Y	0.75...1.25	19.2-0.1	13+0.1	1.25...2	19.4-0.1	13+0.1	2...3	19.8-0.1	13+0.1	
Thickness	X	Y													
0.75...1.25	19.2-0.1	13+0.1													
1.25...2	19.4-0.1	13+0.1													
2...3	19.8-0.1	13+0.1													

CEI <sup>B/N</sup> 701120

14 MAY 2003



Customer No.	No.	Date	Name	Descriptions
SCI No.				
Model No.	R13-516A			
Drawing	Check	Approval		
				
Oct-15-98				

型號

Model No.

R13-516A

動作特性

Switching function(Circuit)

2P SPST OFF-(ON)

規格

Rating

10A125V, 6A250V AC

接觸電阻

Contact Resistance

50m $\Omega$  Max

絕緣電阻

Insulation Resistance

DC 500V 100M $\Omega$  Min

耐電壓

Voltage Breakdown

AC 1500V 1 minute