

Data Sheet

Indestructible 5pcs 5mm LED Headlight 3AAA

17730



Designation: 17730 101 421

Battery Requirement: 3x AAA

Bulb required: 5pcs 5mm cool white LED

Luminous intensity: High: 55 lumens or 225 cd
Low: 21 lumens or 75 cd

Range: 30m High / 17m Low (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)

Weight: 64g (without batteries)

Material: PP (Polypropylene)
ABS (Acrylonitrile Butadiene Styrene)
PC (Polycarbonate)
TPR (Thermoplastic Rubber)
All contact parts made of bronze or nickel plated steel

Dimensions (mm):

A	60
B	40

Run Time: High: 17 hours (with VARTA HE)
Low: 38 hours (with VARTA HE)

Features:

- 30 feet drop test
- 5pcs super bright 5mm cool white LED
- MCU control push switch (High/Low/Off)
- PC material body with over-mould rubber head for maximum durability
- Lighting leakage design when forget to turn off switch
- Compact and lightweight headlight
- 60° pivoting head
- Magnifier lens provide
- Passed extreme temperature shock test
- IPX4 water resistant
- 10,000 Switch cycle life