

Data Sheet

Type Number 6131
Designation IEC CR 11108
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition:..... MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 170 mAh
 Load 5.6 kOhm, at 20°C down to 2.0 V


Weight (approx.) 3 g
Volume 1,1 ccm
Coding..... TBA

Temperature Ranges min max.
 Storage -55°C 70°C
 Discharge -20°C 65°C

Dimensions min max.
 Diameter (A) 11,4 11,6
 Height (B) 10,4 10,8
 Shoulder Diameter[E]..... 7,8
 Shoulder Height [C]..... 0,4

Segment Electronic

Main Applications Photo
 Electronic



Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d, 7d/w Current [μ A]:	5600 Ω	Time:	335 h
		Capacity [mAh]:	170
		Energy [mWh]:	475

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!
 Date of issue:2004-12-16