


C1206C225K5RACTU

aka C1206C225K5RAC7800

Capacitor, ceramic, 2.2 uF, +/-10% Tol, 50V, X7R, 1206



Dimensions (mm)

ID	Dimension	Tolerance
L	3.20	+/-0.20
W	1.60	+/-0.20
T	1.6	+/-0.2
B	0.50	+/-0.25

Specifications

Manufacturer:	KEMET
Capacitance:	2.2 uF
Chip Size:	1206
Voltage:	50V
Temperature Coefficient:	X7R
Tolerance:	+/-10%
Application:	Std Chip
Termination Type:	Tin
Marked:	No
Dissipation Factor:	2.5%
Insulation Resistance:	454.55 MOhm
Dielectric Strength:	125V
Miscellaneous Electrical:	Regarding Aging Rate: Capacitance measurements (including tolerance) are indexed to a referee time of 1000 hours
Package Kind:	T&R
Package Size:	7in
Package Type:	Plastic Tape
Package Quantity:	2000