



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 12

PATTEX 60 SECOND FORMULA

SDS No. : 412836
V002.1

Revision: 22.05.2015

printing date: 03.11.2015

Replaces version from: 16.07.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Pattex Kraft-Mix Power-Mix Express Super Rapide 1 Min, Komp. A

Contains:

Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700)

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Part A of 2-K-Epoxy Adhesive

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 (211) 797 0

Fax-no.: +49 (211) 798 4008

ua-productsafety.de@henkel.com

1.4. Emergency telephone number

The Henkel information service also provides an around-the-clock telephone service on phone no.+49-(0)211-797-3350 for exceptional cases.

Further information is available at Poison Control Centers.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Chronic hazards to the aquatic environment	Category 2
H411 Toxic to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:**Signal word:**

Warning

Hazard statement:

H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

Precautionary statement:

P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.

**Precautionary statement:
Prevention**

P280 Wear protective gloves/eye protection.

**Precautionary statement:
Disposal**

P501 Dispose of contents/container in accordance with national regulation.

2.3. Other hazards

Persons suffering from allergic reactions to epoxides should avoid contact with the product.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Reaction resin

Base substances of preparation:

Epoxy resin

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	500-033-5 500-033-5 01-2119456619-26	> 90 %	Skin Irrit. 2 H315 Skin Sens. 1 H317 Eye Irrit. 2 H319 Aquatic Chronic 2 H411

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures****General information:**

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing. If necessary, see a dermatologist.

Eye contact:

Immediately flush eyes with soft jet of water or eye rinse solution for at least 5 minutes. If pain remains (intensive smarting, sensitivity to light, visual disturbance) continue flushing and contact/seek doctor or hospital.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

May cause an allergic skin reaction.

Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

Avoid contact with skin and eyes.

Danger of slipping on spilled product.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove with liquid-absorbing material (sand, peat, sawdust).

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container.

Store frost-free.

Store protected from heat influence.

Temperatures between + 5 °C and + 30 °C

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Part A of 2-K-Epoxy Adhesive

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**Valid for
Germany

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (freshwater)					0,006 mg/L	
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (marine water)					0,0006 mg/L	
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (intermittent releases)					0,018 mg/L	
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	STP					10 mg/L	
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (freshwater)				0,996 mg/kg		
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (marine water)				0,0996 mg/kg		
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	soil				0,196 mg/kg		
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	oral					11 mg/kg food	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Dermal	Acute/short term exposure - systemic effects		8,33 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Inhalation	Acute/short term exposure - systemic effects		12,25 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Dermal	Long term exposure - systemic effects		8,33 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Inhalation	Long term exposure - systemic effects		12,25 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Dermal	Acute/short term exposure - systemic effects		3,571 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Dermal	Long term exposure - systemic effects		3,571 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Inhalation	Acute/short term exposure - systemic effects		0,75 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Inhalation	Long term exposure - systemic effects		0,75 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	oral	Acute/short term exposure - systemic effects		0,75 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	oral	Long term exposure - systemic effects		0,75 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:Respiratory protection:
Not needed.

Hand protection:

In the case of longer contact protective gloves made from nitrile rubber are recommended according to EN 374.

Perforation time > 480 minutes

material thickness > 0.1 mm

In the case of longer and repeated contact please note that in practice the penetration times may be considerably shorter than those determined according to EN 374. The protective gloves must always be checked for their suitability for use at the specific workplace (e.g. mechanical and thermal stress, product compatibility, antistatic effects, etc.). The gloves must be replaced immediately at the first signs of wear and tear. The information provided by the manufacturers and given in the relevant trade association regulations for industrial safety must always be observed. We recommend that a hand care plan is drawn up in cooperation with a glove manufacturer and the trade association in accordance with the local operating conditions.

Eye protection:

Goggles which can be tightly sealed.

Skin protection:

Suitable protective clothing

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid high viscosity transparent
Odor	typical
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density (23 °C (73.4 °F))	1,1 - 1,2 g/cm ³
Bulk density	No data available / Not applicable
Viscosity (Brookfield; 23 °C (73.4 °F))	14.000 - 24.000 mPa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reacts with amines, alcohols, acids and alkalis.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

Persons suffering from allergic reactions to epoxides should avoid contact with the product.

Cross-reactions with other epoxide compounds possible.

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye irritation.

Sensitizing:

May cause an allergic skin reaction.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LD50	> 2.000 mg/kg	oral		rat	

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LD50	23.000 mg/kg	dermal		rabbit	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	slightly irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sensitising	Mouse local lymphnod e assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	negative	bacterial reverse mutation assay (e.g Ames test)			OECD Guideline 472 (Genetic Toxicology: Escherichia coli, Reverse Mutation Assay)

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Toxic to aquatic life with long lasting effects.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LC50	1,750000 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
	LC50	1,75 mg/l	Fish	96 h	Oncorhynchus mykiss (reported as Salmo gairdneri)	OECD Guideline 203 (Fish, Acute Toxicity Test)
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	NOEC	2,4 mg/l	Algae	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
	EC50	9,4 mg/l	Algae	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	NOEC	0,3 mg/l	chronic Daphnia	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

12.2. Persistence and degradability

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
---------------------------------	--------	-------------------------	---------------	--------

Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6		aerobic	5 %	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
--	--	---------	-----	---

12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information**14.1. UN number**

ADR	3082
RID	3082
ADN	3082
IMDG	3082
IATA	3082

14.2. UN proper shipping name

ADR	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
RID	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
ADN	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
IMDG	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
IATA	Environmentally hazardous substance, liquid, n.o.s. (Bisphenol-A Epichlorhydrin resin)

14.3. Transport hazard class(es)

ADR	9
RID	9
ADN	9
IMDG	9
IATA	9

14.4. Packaging group

ADR	III
RID	III
ADN	III
IMDG	III
IATA	III

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	Marine pollutant
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode: (E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0 %

(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

National regulations/information (Germany):

WGK: 2, water-endangering product. (German VwVwS of May 17, 1999)
Classification in conformity with the calculation method

BG regulations, rules, infos:

BG information : Guidance document for the handling of epoxy resins.

Storage class according to TRGS 510: 10

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Label elements (DPD):

Xi - Irritant

N - Dangerous for the environment



Risk phrases:

R36/38 Irritating to eyes and skin.

R43 May cause sensitisation by skin contact.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

S2 Keep out of the reach of children.

S24/25 Avoid contact with skin and eyes.

S29 Do not empty into drains.

S37 Wear suitable gloves.

S46 If swallowed, seek medical advice immediately and show this container or label.

Additional labeling:

Contains epoxy constituents. See information supplied by the manufacturer.

Contains:

Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700)

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 8

PATTEX 60 SECOND FORMULA

SDS No. : 412835
V002.1

Revision: 22.05.2015
printing date: 03.11.2015
Replaces version from: -

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Pattex KraftMix Schnell 1min Spritze,K.B

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Part B of 2-Component Epoxy Adhesive.

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA
Henkelstr. 67
40589 Düsseldorf

Germany

Phone: +49 (211) 797 0
Fax-no.: +49 (211) 798 4008

ua-productsafety.de@henkel.com

1.4. Emergency telephone number

The Henkel information service also provides an around-the-clock telephone service on phone no.+49-(0)211-797-3350 for exceptional cases.

Further information is available at Poison Control Centers.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.3. Other hazards

Persons suffering from allergic reactions to amines should avoid contact with the product.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Hardener

Base substances of preparation:

Polymercaptan

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
1,3-bis[3-(dimethylamino)propyl]urea 52338-87-1	257-861-2	< 7 %	Skin Irrit. 2; Dermal H315 Eye Irrit. 2 H319
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	229-713-7	< 3 %	Acute Tox. 3; Oral H301 Skin Corr. 1A H314 Aquatic Chronic 3 H412

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures**

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water, seek medical advice if necessary.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

Danger of slipping on spilled product.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove with liquid-absorbing material (sand, peat, sawdust).

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly sealed.

Temperatures between + 10 °C and + 25 °C

Store at room temperature.

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Part B of 2-Component Epoxy Adhesive.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Germany

None

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:
Not needed.

Hand protection:

In the case of longer contact protective gloves made from nitrile rubber are recommended according to EN 374.

Perforation time > 480 minutes

material thickness > 0.1 mm

In the case of longer and repeated contact please note that in practice the penetration times may be considerably shorter than those determined according to EN 374. The protective gloves must always be checked for their suitability for use at the specific workplace (e.g. mechanical and thermal stress, product compatibility, antistatic effects, etc.). The gloves must be replaced immediately at the first signs of wear and tear. The information provided by the manufacturers and given in the relevant trade association regulations for industrial safety must always be observed. We recommend that a hand care plan is drawn up in cooperation with a glove manufacturer and the trade association in accordance with the local operating conditions.

Eye protection:

Goggles which can be tightly sealed.

Skin protection:

Suitable protective clothing

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	liquid high viscosity transparent
Odor	typical
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	Not available.
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density (20 °C (68 °F))	1,09 - 1,19 g/cm ³
Bulk density	No data available / Not applicable
Viscosity (Brookfield; 23 °C (73.4 °F); speed of rotation: 20 min ⁻¹ ; Spindle No: 6)	15.000 - 20.000 pa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (23 °C (73.4 °F); Solvent: Water)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

Persons suffering from allergic reactions to amines should avoid contact with the product.

Cross-reactions with other amine compounds are possible.

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
1,3-bis[3-(dimethylamino)propyl]urea 52338-87-1	LD50	> 5.000 mg/kg	oral			

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
1,8-Diazabicyclo[5.4.0]undec- 7-ene 6674-22-2	LC50	> 100 - 220 mg/l	Fish	96 h	Leuciscus idus	OECD Guideline 203 (Fish, Acute Toxicity Test)
1,8-Diazabicyclo[5.4.0]undec- 7-ene 6674-22-2	EC50	50 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

12.2. Persistence and degradability

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
1,8-Diazabicyclo[5.4.0]undec- 7-ene 6674-22-2		aerobic	< 20 %	OECD Guideline 301 A (new version) (Ready Biodegradability: DOC Die Away Test)

12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

08 04 10 Waste adhesives and sealants other than those mentioned in 08 04 09.

SECTION 14: Transport information**14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	3334

14.2. UN proper shipping name

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Aviation regulated liquid, n.o.s. (Mercaptan polymer)

14.3. Transport hazard class(es)

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	9

14.4. Packaging group

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	III

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	No dangerous good according to ADR/RID/ADN. Carriage in accordance with 1.1.4.2.1 ADR/RID/ADN.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0 %
(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

National regulations/information (Germany):

WGK: 2, water-endangering product. (German VwVwS of May 17, 1999)
Classification in conformity with the calculation method
Storage class according to TRGS 510: 10

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H301 Toxic if swallowed.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H412 Harmful to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Label elements (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.